




TIME DIVISION MULTIPLEXING/ DEMULTIPLEXING USING PAM

MODEL- COM109S

This trainer has been designed with a view to provide practical and experimental knowledge of 4 channel Time Division Multiplexing Demultiplexing using PAM technique on a SINGLE PCB.



SPECIFICATIONS

1. Power supply requirement : 230V AC, 50 Hz.
2. Crystal control clock
3. On Board sine wave & digital signal generators.
4. 4 Channel Time division multiplexing demultiplexing (analog)
5. 16 Channel Time division multiplexing demultiplexing (digital)
6. Manchester coding decoding
7. Pulse position modulation
8. Can used with fiber optic & various other communication links
9. The parts soldered on the front side of SINGLE PCB with complete circuit diagram screen printed.
10. Standard Accessories :
 1. A Training Manual.
 2. Connecting Patch cords.

In keeping view of SIGMA policy of continuous development and improvement, the Specifications may be changed without prior notice or obligation.

Sigma Trainers and Kits
E-113, Jai Ambe Nagar,
Near Udgam School,
Thaltej,
AHMEDABAD - 380054.
INDIA.

Phone(O): +91-79-26852427/ 26850829
Phone(F): +91-79-26767512/ 26767648
Fax : +91-79-26840290/ 26840290
Mobile : +91-9824001168
Email : sales@sigmatrainers.com
: sigmatrainers@sify.com
Web : www.sigmatrainers.com

Dealer:-