


QUADRATURE AMPLITUDE MODULATION/ **DEMODULATION TRAINER**

MODEL - OAM100L

This trainer has been designed with a view to provide practical/experimental knowledge of QAM Modulation/Demodulation technique as practically implemented in Digital Communication systems on a SINGLE PCB.



SPECIFICATIONS

Power supply requirement 230V AC, 50 Hz. 1.

Built in IC based power supply. 2.

On Board Modulating Digital Data signal generator to generate any binary input word with Bit clock & Word 3.

clock.

Bit Clock Frequency 80 KHz. Word Clock Frequency 10 KHz. Word Length 8 Bits.

Data Format NRZ, 0° (I) and 90° (Q) signals.

4. **Modulator Type** Balanced Modulator as QAM modulator. 5. Demodulator Type Balanced Modulator as QAM demodulator. All parts are soldered on single PCB with complete circuit diagram Screen-printed. 5.

Standard Accessories 1. A Training Manual

2. Connecting Patch cords.

EXPERIMENTS

- To study theory of QAM Modulation & Demodulation. 1.
- To generate QAM signal and demodulate it 2.
- To observe QAM modulated output by for different input binary codes. 3.

In keeping view of SIGMA policy of continuous development and improvement, the Specifications may be changed without prior notice or obligation.

Sigma Trainers and Kits

E-113, Jai Ambe Nagar, Near Udgam School,

Thaltej,

AHMEDABAD - 380054.

INDIA.

Phone(O): +91-79-26852427/ 26850829

Phone(F): +91-79-26767512/ 26767648

: +91-79-26840290/ 26840290

Mobile : +91-9824001168

Email: sales@sigmatrainers.com

: sigmatrainers@sify.com

Dealer:-

Web : www.sigmatrainers.com