


## **MULTI VIBRATORS TRAINER**

## MODEL MULTIDM100

Multivibrator Trainer Model Multi100 is a self-contained unit, which can be used to perform different types of Multivibrator configurations.



**SPECIFICATIONS** 

- 1. The complete circuit is printed on a single P.C.B.
- 2. All parts are soldered on single pin tag for easy replacement.
- 3. Explanation, Observation, Alignment and adjustment of Internal and external controls is possible due to Single P.C.B.
- 4. Easy identification of different parts is possible at a glance.
- 5. Easy measurement of voltages and observation of waveforms at any point. Test Points are provided on P.C.B.
- 6. Built-in Power supply : +15V at 200mA IC Regulated & short circuit protected
- 7. Power requirement

: 230V, 50Hz AC.

8. Standard Accessories

- : 230V, 50HZ AC.
- : 1.A manual having practical details.
- : 2. Patch Cords.

## EXPERIMENTS

1. Design of multivibrators.

- 2. To study the waveforms of a free running multivibrator
- 3. To design and make a bistable multivibrator and to study its D.C. conditions.
- 4. To design and make a monostable multivibrator and to adjust its delay time.
- 5. To design and make schmitt-trigger and study its hysteresis.
- 6. To control the frequency of a free running multivibrator with applied voltage.
- 7. To design and make a gated free running multivibrator.
- 8. To design and make an improved free running multivibrator.

In keeping view of SIGMA policy of continuous development and improvement, the Specifications may be changed without prior notice or obligation.

## Sigma TrainersPhone<th:079-26852427/26767512</th>Dealer:-E-103, Jai Ambe Nagar,<br/>Near Udgam School, Thaltej,<br/>AHMEDABAD - 380054.Phone: 079-26859162/26853758Dealer:-Web: sales@sigmatrainers@com<br/>: sigmatrainers@com<br/>Web: www.sigmatrainers.comDealer:-