



TWILIGHT CONTROL USING 555 AND LDR

MODEL OPT012

This trainer has been designed with a view to provide practical and experimental knowledge of Twilight Control using 555 and LDR.

SPECIFICATIONS

1. Power supply requirement : 230V AC, 50 Hz.
2. Built in IC based regulated Power supply : +12VDC/200 mA.
3. Following parts provided on Single PCB with connecting terminals.
LDR - 1 No.
Relay 1 No.
4. External AC Lamp to apply light on LDR.
5. Standard Accessories :
 1. User Manual with practical and circuit diagrams.
 2. Connecting patch cords.

In keeping view of SIGMA policy of continuous development and improvement, the Specifications may be changed without prior notice or obligation.

Sigma Trainers
E-103, Jai Ambe Nagar,
Near Udgam School, Thaltej,
AHMEDABAD - 380054.

Phone : 079-26852427 / 26767512
Fax : 079-26840290 / 26759661
ISDN : 079-26859162 / 26853758
Email : sales@sigmatrainers.com
: sigmatrainers@sify.com
Web : www.sigmatrainers.com

Dealer:-